





Item Number
60110-469

Single phase monitored PDU

Input Rating : 32A, 230V
Outlet : 10A Rated C13 x 20
16A Rated C19 x 4
Inlet : 32A IEC60309 2P+E plug
Cordset : 3 meter 4mm sq. H05V V-F cordset
Protection : 16A resettable fuse x 2
Circuit Details : < **Circuit A** > Output 16A max. C 13 # 1 - 10 + C 19 # C1 - C 2
< **Circuit B** > Output 16A max. C 13 # 11 - 20 + C 19 # C3 - C 4

Meter Features (W monitored PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
Accuracy : ±1% Billing-grade
IP Access : via IP dongle, one IP Access up to 16 PDU Levels
Cascade : Up to 16 PDU under single IP address via IP dongle
SNMP : V2 / V3 via IP dongle
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : CE / EMC certified
Safety Compliance : CE / LVD certified
Environment Compliance : RoHS2 & REACH
Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing


Chassis Material : Steel
Chassis Color : Black

Product Dimension : 54 (W) x 80 (D) x 1350 (H) mm
Net Weight : 5.6 kg

Packing Dimension (for 2 PDUs) : 110 (W) x 268 (D) x 2043 (H) mm
PDU Gross Weight (for 2 PDUs) : 14.8 kg

Mounting Method

VMS :



VMB :

Top feed

Bottom feed

