



SCHROFF

MWA245-3.80HLR 245 CARD-LOK



KEY FEATURES

3 segment, non-shafted design

Profile 6.60 mm (0.260") x 6.86 mm (0.270")

Screw actuated

Length 97 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

DSCC CID 59590

Min expansion 8.26 mm (0.325")

Weight 1.77 g/cm (0.159 oz/')

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

Flexible mounting options

For cold wall applications

Average clamp force (4.80", black anodized) = 470 lbs

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Type: Non-shafted

Thermal Performance: Good

Profile: 0.260" x 0.270" / 6.60 x 6.86 mm

Clamp Force: 400 – 499 lbf / 181 – 226 kg

Gap Width: PCB + (0.28 - 0.31 in) / PCB + (7.0 - 7.9 mm)

ADDITIONAL PRODUCT DETAILS

The Series 245 features a 6-32 screw to provide greater clamping force and load capacities than other Card Loks of similar profiles.

⚠️WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

CERTIFICATIONS



North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.