

Northbrook, Illinois • (847) 272-8800
 Melville, New York • (516) 271-6200
 Santa Clara, California • (408) 985-2400
 Research Triangle Park,
 North Carolina • (919) 549-1400
 Camas, Washington • (360) 817-5500



SCHROFF GMBH
 UL COORDINATOR-ENGINEERING SEC
 POSTFACH 3
 75332 STRAUBENHARDT FED REP GERMANY

EINGEGANGEN
 - 2. Nov. 1999
 Erl.....

RE: Project Number(s) - 98ME31310

Your most recent listing is shown below. Please review this information and report any inaccuracies to the UL Engineering staff member who handled your project.

For information on placing an order for UL Listing Cards in a 3 x 5 inch format, please refer to the enclosed ordering information.

QQGQ2 October 19, 1999
 Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

SCHROFF GMBH
 POSTFACH 3, 75332 STRAUBENHARDT FED REP GERMANY

E153809

Model No.	Rated Input		SC	Output			OC	SP	EP	FC	GC
	V	Hz		Max V	Max A	Max VA					
SFM 105(@)	100-120/ 220-240	50-60	0	5	12	—	3	1950	—	0	—
SFM 112(@)	100-120/ 220-240	50-60	0	12	5.6	—	3	1950	—	0	—
SFM 115(@)	100-120/ 220-240	50-60	0	15	4.5	—	3	1950	—	0	—
SFM 124(@)	100-120/ 220-240	50-60	0	24	2.8	—	3	1950	—	0	—
SPG 105(@)	100-120/ 220-240	50-60	0	5	22	—	3	1950	—	0	—
SPG 112(@)	100-120/ 220-240	50-60	0	12	11.6	—	3	1950	—	0	—
MPS 022	110-230	50-60	0	12	33.5	154	3	1950	—	0	—
MPS 022/15	110-230	50-60	0	15	36	144	3	1950	—	0	0
MPS 015	110-230	50-60	0	15	32	157	3	1950	—	0	0
MPS015/15											
PSG212	200-240	50-60	0	16.4	26	426.4	3	1950	—	0	0
13195-002				16.4	26	426.4					
PSG215	200-240	50-60	0	15	0.2	—	3	1950	—	0	0
13195-003				15	0.2	—					
SPG 115(@)	100-120/ 220-240	50-60	0	15	9.3	—	3	1950	—	0	—
SPG 124(@)	100-120/ 220-240	50-60	0	24	5.8	—	3	1950	—	0	—
SPF105(@)	100-120	50-60	0	5	16	—	3	1950	—	0	—
SPF112(@)	100-120	50-60	0	12	8.3	—	3	1950	—	0	—
SPF115(@)	100-120	50-60	0	15	6.6	—	3	1950	—	0	—
SPF124(@)	100-120	50-60	0	24	4.2	—	3	1950	—	0	—