



Item Number  
**60110-457**

### Single phase switched + outlet measurement PDU

Input Rating : 16A, 230V  
Outlet : 10A Rated C13 x 20  
Inlet : 16A IEC60309 2P+E plug  
Cordset : 3 meter 1.5mm sq. H05V V-F cordset  
Protection : 16A resettable fuse x 1  
Circuit Details : Output 16A max. C13 #1-20

### Residual Current Monitoring

Measuring Range : 0 to 300 mA ( RMS )  
Measurement Accuracy : 0 to 15%  
Rated Frequency : 50 / 60 Hz  
Response Time : < 10 sec

### Meter Features ( WSi Switched PDU + Outlet Measurement )

Local Display : Field replaceable 2.8" color LCD with touchscreen  
Bank Measurement : Current ( A ), Energy ( kWh ), Voltage ( V ) & Power factor  
Outlet Measurement : Current ( A ), Energy ( kWh )  
Outlet Control : Outlet Switch ON / OFF  
Accuracy : ±1% Billing-grade  
IP Access : via IP dongle, one IP Access up to 16 PDU Levels  
Cascade : Up to 16 PDU under single IP address via IP dongle  
SNMP : V2 / V3 via IP dongle  
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : CE / EMC certified  
Safety Compliance : CE / LVD certified  
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C  
Storage Temperature : -25 to 65 °C  
Operating Altitude : 0 to 2,000 m  
Storage Altitude : 0 to 15,000 m  
Humidity : 8 to 95% RH, non-condensing

Chassis Material : Steel  
Chassis Color : Black

Product Dimension : 54 (W) x 80 (D) x 1350 (H) mm  
Net Weight : 6.5 kg

Packing Dimension ( for 2 PDUs ) : 110 (W) x 268 (D) x 2043 (H) mm  
PDU Gross Weight ( for 2 PDUs ) : 16.2 kg