

The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.

Toute communication ou reproduction de ce document, toute exploitation ou communication de son contenu sont interdites, sauf autorisation expresse. Tout manquement à cette règle est illicite et expose son auteur au versement de dommages et intérêts. Tous droits réservés pour le cas de la délivrance d'un brevet, d'un modèle d'utilité ou d'un modèle de présentation.

Dessin des connecteurs et de la jonction non contractuels
Plug and junction drawing not contractual

Connecteur EN60320/C13 surmoulé noir
Molded black connector EN60320/C13





Schéma de câblage
Cabling scheme



Composition à la livraison:

- Câble EN Y
- Notice 60118-516
- Emballage sachet thermo soudé avec numéro d'article SCHROFF et code barre 39.

Deliver composition:

- Y cable
- User manual 60118-516
- Heat-weldable packaging bag with SCHROFF's article number and bar code 39.

Utilisation initiale / Initial use	VARISTAR	Echelle / Scale	1:1	Surface / Surface	. mm ²	Volume / Volume	. mm ³	Masse / Mass	. g
Matière / Material	[A001]: pas précise / NA								
Pièce de base / Basic-part	Epaisseur / Thickness NA								
Libérer / Approved	28.04.2005	STEINM	Désignation / Designation						
Norme / Conformity			CORDON ALIMENTATION Y IEC						
Vérifier / Checked	28.04.2005	LEDIG	Title / Titre						
Dessiner / Drawn	28.04.2005	STEINM	CONNECTION CABLE Y WITH IEC						
Index / Rev.	ECO-No / ECO-No	Date / Date	Nom / Name	No du plan / Drawing no.				Dimensions en mm / Dimensioning in mm	
B	Ideas>SWX	03.08.2011	PISKOR	62150-201_BET				Schroff®	
				Modèle 3D / 3D-Model				Page / Sheet	
				62150-201_BET				1/1	
				Std Origin Item: 62150-201_BET				Schroff S.A.S Z.I. 4.Rue des Marais F-67660 Betschdorf	