



Item Number
60110-457

Single phase switched + outlet measurement PDU		Residual Current Monitoring		Meter Features (WSi Switched PDU + Outlet Measurement)		EMC Compliance	
Input Rating	: 16A, 230V	Measuring Range	: 0 to 300 mA (RMS)	Local Display	: Field replaceable 2.8" color LCD with touchscreen	Safety Compliance	: CE / EMC certified
Outlet	: 10A Rated C13 x 20	Measurement Accuracy	: 0 to 15%	Bank Measurement	: Current (A), Energy (kWh), Voltage (V) & Power factor	Environment Compliance	: CE / LVD certified
Inlet	: 16A IEC60309 2P+E plug	Rated Frequency	: 50 / 60 Hz	Outlet Measurement	: Current (A), Energy (kWh)		: RoHS2 & REACH
Cordset	: 3 meter 1.5mm sq. H05V V-F cordset	Response Time	: < 10 sec	Outlet Control	: Outlet Switch ON / OFF	Operating Temperature	: -5 to 60 °C
Protection	: 16A resettable fuse x 1			Accuracy	: ±1% Billing-grade	Storage Temperature	: -25 to 65 °C
Circuit Details	: Output 16A max. C 13 # 1 - 20			IP Access	: via IP dongle, one IP Access up to 16 PDU Levels	Operating Altitude	: 0 to 2,000 m
				Cascade	: Up to 16 PDU under single IP address via IP dongle	Storage Altitude	: 0 to 15,000 m
				SNMP	: V2 / V3 via IP dongle	Humidity	: 8 to 95% RH, non-condensing
				Sensor Port x 2	: Temp. Sensor / Temp. + Humid. Sensor	Chassis Material	: Steel
						Chassis Color	: Black
						Product Dimension	: 54 (W) x 80 (D) x 1350 (H) mm
						Net Weight	: 6.5 kg