



ONLINE CONFIGURATOR SCOPE

Version	Date	Originator	Description
1.00	22/06/2021	Franck Perrot	Release

Table of contents

Novastar Online configurator 3

Varistar Online configurator 4

Subrack Online configurator 5

Front panel Online configurator 6

Cardlok & Wedge lok Online configurator 7

Novastar Online configurator



What	Valid
Slim Line frame	☒
Heavy Duty frame	☒
Universal frame	
IP protection	☒
Shortened doors	☒
Heat management acc.	☒
Power distribution	
Color change	☒
Mechanical modification	☒
Wizard functionality	
Instant pricing	☒
Full process automation	☒

Slim Line												
Height	Unit	6	9	12	16	20	25	34	38	43	47	
Width	mm	553										
Depth	mm	500	600	800	900	1000						
19" recess	mm	33	60	85								
Heavy Duty												
Height	Unit	6	9	12	16	20	25	34	38	43	47	
Width	mm	553										
Depth	mm	500	600	800	900	1000						
19" recess	mm	33	60	85								
Universal												
Height	Unit	6	9	12	16	20	25	34	38	43	47	
Width	mm	553										
Depth	mm	500	600	800	900	1000						
19" recess	mm	33	60	85								

Delivery: assembled

Varistar Online configurator



What	Valid
Slim Line frame	☒
Heavy Duty frame	☒
Seismic frame	☒
MIL frame	
IP protection	☒
EMC protection	☒
Fire & smoke protection	☒
Shortened doors	☒
Heat management acc.	
Power distribution	
Color change	☒
Mechanical modification	☒
Wizard functionality	
Instant pricing	☒
Full process automation	☒

Slim Line								
Height	Unit	24	29	33	38	42	47	52
Width	mm	600	800					
Depth	mm	600	800	900	1000	1100	1200	
19" recess	mm	50	70	145	220			
Heavy Duty								
Height	Unit	24	29	33	38	42	47	52
Width	mm	600	800					
Depth	mm	600	800	900	1000	1100	1200	
19" recess	mm	50	70	145	220			
Seismic								
Height	Unit	24	29	33	38	42	47	52
Width	mm	600	800					
Depth	mm	600	800	900	1000	1100	1200	
19" recess	mm	50	70	145	220			

Delivery: assembled

Subrack Online configurator



What	Valid
Light type	☒
Flexible type	☒
Heavy type	☒
Rugged type	☒
Railway type	
cPCI type	
EMC version	☒
Backplane Insulated mounting	☒
Backplane Direct mounting	☒
Connector mounting	☒
Split in height (2 * 3U)	☒
Combined mounting kit	
Horizontal mounting kit	
Mounting plate	
Rear panel / cover	☒
Color modification	
Modification module	
Wizard functionality	☒
Instant pricing	☒
Full process automation	

Light							
Height	Unit	3	6				
Width	HP	28	42	63	84		
Depth	mm	175	235	295	355	415	475
Flexible							
Height	Unit	3	6				
Width	HP	28	42	63	84		
Depth	mm	175	235	295	355	415	475
Heavy							
Height	Unit	3	6				
Width	HP	28	42	63	84		
Depth	mm	175	235	295	355	415	475
Rugged							
Height	Unit	3	6				
Width	HP	28	42	63	84		
Depth	mm	175	235	295	355	415	475

Delivery: assembled

Front panel Online configurator



What	Valid
19" type	☒
Filler type	☒
Bottom hinged type	☒
Side hinged type	☒
IEL handle type	☒
IET handle type	☒
XL handle type	☒
Type 1 handle	
Type 2 handle	☒
Key form 1	
Key form 2	
Static handle	☒
Static AI profile handle	
EMC version	☒
Microswitch	☒
Rear i/o	
0.1" offset	
Color modification	☒
Modification module	☒
Wizard functionality	☒
Instant pricing	☒
Full process automation	☒

Delivery: assembled

Filler type																				
19"	Unit	1	2	3	4	5	6	7	8	9	10									
Filler modular	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84
Bottom hinged	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84
Side hinged	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84
Handle type																				
IEL/IET	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84
XL	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84
Type 2	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84
Static	Unit	1	2	3	4	5	6	7	8	9	10									
	HP	1	2	3	4	5	6	7	8	9	10	11	12	14	16	21	28	42	63	84

Cardlok & Wedge lok Online configurator



Average Thermal performance

PCB .20 to .23

inch 5 to 5,9mm

Serie 240	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 41	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12

PCB .24 to .27

inch 6 to 6,9mm

Serie 230	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 266	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 42	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12
Serie 42-5	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12

PCB .28 to .31

inch 7 to 7,9mm

Serie 223	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 225	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 245	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 261	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 40	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12
Serie E225	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

PCB .32 to .35

inch 8 to 8,9mm

Serie 224	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 235	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 236	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

PCB .39 to .43

inch 10 to 10,9mm

Serie 250	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 281	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

High Thermal performance

PCB .20 to .23 inch 5 to 5,9mm

Serie 267	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 267HC	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 41-5	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12

PCB .24 to .27 inch 6 to 6,9mm

Serie 265	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 265HC	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 265HTS	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

PCB .28 to .31 inch 7 to 7,9mm

Serie 260	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 260HC	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 40-5	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12
Serie 48-5	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12
Serie 48SL-5	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12
Serie 260HTS	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

PCB .32 to .35 inch 8 to 8,9mm

Serie 263	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 263HC	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

PCB .39 to .43 inch 10 to 10,9mm

Serie 280	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
Serie 44-5	inches	2	2,5	3	3,5	4	4,5	5	6	6	7	7	8	8	9	9	10	10	11	11	11,5	12
Serie 280HTS	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8

PCB .51 to .55 inch 13 to 13,9mm

Serie 255	inches	2,8	3,3	3,8	4,3	4,8	5,3	6	6	7	7	8	8	9	9	10	10	11	11	12	12,3	12,8
-----------	--------	-----	-----	-----	-----	-----	-----	---	---	---	---	---	---	---	---	----	----	----	----	----	------	------

