

Series 35-6 PCB-Tainer

CONNECT AND PROTECT




WEIGHT

.37g/cm (.033 oz/in)






MATERIALS AND FINISH

HOUSING


- **Material:** .008-in. (.20-mm) thick Beryllium Copper per ASTM B-194 or Stainless Steel per ASTM A-366
- **Finish:** See finish table on opposite page



Units: mm (in)
Unless specified otherwise,
.xx = $\pm .25$, x = $\pm .5$
(.xxx = $\pm .010$, .xx = $\pm .02$)



MOUNTING HOLE DETAIL



FLARED ENTRY OPTION DETAIL

Part Number Code	
Series 35-6 PCB	35 C F -6 B -2 -10 -5
Center Mounting Hole	
Center Mounting Hole _____ C	
None _____ [Blank]	
Flared Entry	
Flared Entry: _____ F	
None: _____ [Blank]	
Material	
Beryllium Copper _____ B	
or select from Materials Table	
Board Thickness	
1.59 (.063) PCB Thickness _____ 2	
or select from Dimension Table	
Length	
Length in 12.7 (.50) increments _____ 4 [50.8 (2.00)]	
_____ to 12 [152.4 (6.00)]	
Finish	
Gold Plate _____ 5	
or select from Finish Table	
No dash number required for CR material. Stainless steel parts are passivated only.	

Part Number Code example:

35F-6B-3-10-6

35 Series PCB-TAINER, Beryllium Copper with Flared Entry, 2.38-mm (.094-in.) thick board, 127.0-mm (5.00-in.) long, nickel plate finish.

MATERIALS TABLE

CODE LETTER	MATERIAL
B	BERYLLIUM COPPER, 1/4H PER ASTM-B-194
BH	BERYLLIUM COPPER, 1/4HT PER QQ-C-533, HEAT TREATED
CR	STAINLESS STEEL, TYPE 301 COND 1/4 H PER AMS 5517

FINISH TABLE

Dash #	MATERIAL
[Blank]	SILVER PLATE PER QQ-S-365, TYPE III, GRADE A
-1	NONE
-2	EBANOL PER MIL-F-495 FOR BERYLLIUM COPPER PER MIL-C-13924 FOR STEEL
-3	CADMIUM PER QQ-P-416, TYPE 2, CLASS 2
-4	COPPER PLATE PER MIL-C-14550, CLASS 2
-5	GOLD PLATE PER MIL-G-45204, TYPE 1, GLASS 1
-6	NICKEL PLATE PER QQ-N-290, CLASS 1, GRADE G, BRIGHT
-7	ZINC PLATE CLEAR CHROMATE, PER ASTM-B-633, Fe/Zn 8
-8	ZINC PLATE YELLOW CHROMATE, PER ASTM-B-633, Fe/Zn 8

DIMENSION TABLE

BOARD THICKNESS

DASH #	A	B	C MAX	D	E
-1	0.79 (.031)	4.58 (.180)	8.39 (.330)	7.57 (.298)	3.97 (.156)
-2	1.59 (.063)	4.58 (.180)	8.39 (.330)	7.57 (.298)	3.97 (.156)
-3	2.38 (.094)	4.58 (.180)	8.39 (.330)	7.57 (.298)	3.97 (.156)
-4	3.18 (.125)	4.58 (.180)	9.40 (.370)	8.39 (.330)	3.97 (.156)

nVent SCHROFF, Inc.

7328 Trade Street San Diego,
CA 92121 USA
+1 800-525-4682

BIRTCHETM



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER