


Series 125, 126 Retainers

CONNECT AND PROTECT



WEIGHT

.40 g/cm (.036 oz/in)

MATERIALS AND FINISH


- **Material:**
.41 (.016) thick Stainless Steel Type 301, Cond.
1/2 H, ASTM -A240
- **Finish:**
Passivated per MILS-5002

SPRING RATE

60.4N/cm (34.5lbs/in)
of deflection per spring finger

| Dash No. | PCB Thickness | B Dimension +0.38 (.015) -0.0 (.000) | G Dimension +0.0 (.00) -0.80 (.03) |
|----------|---------------|--|--|
| -06 | 1.6 (1/16) | 1.91 (.075) | 1.14 (.045) |
| -09 | 2.4 (3/32) | 2.67 (.105) | 1.91 (.075) |

125 Shown, 126 Opposite



| Part Number Code | | | |
|------------------------------------|--|------------|------------|
| PCB Thickness | | 125 or 126 | -06 - 3.25 |
| 1.6 (.063) | | 06 | |
| 2.4 (.094) | | 09 | |
| Length | | | 3.25 |
| 31.75 (1.25) to 311.15 (12.25) | | | |
| in 25.4 (1.00) increments | | | |
| Other lengths available on request | | | |

Part Number Code Example:

125-06-4.25
Series 125 passivated stainless steel,
107.95 (4.25) long designed for 1.6 (.063)
thick printed circuit boards

nVent SCHROFF, Inc.

7328 Trade Street
San Diego, CA 92121 USA
+1 800-525-4682

CALMARK™



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER