

# Model: RP2850

32/30 A (24 A derated), 380 – 415 VAC, 3-phase Wye



## Input Metered, Outlet Switched PDU Data Sheet – RackPower PDU

The RP2850 Input Metered, Outlet Switched PDU combines energy metering, power and environmental monitoring with remote outlet on/off switching to monitor, protect, and manage the rack environment. Utility grade metering at the phase input and internal circuit breaker levels provides comprehensive overload monitoring. Outlet power-up sequencing protects against inrush current overload and allows users to define equipment boot-up order and timing. While remote on/off control allows authorized users to power-cycle remote equipment and implement rack-level power access controls to power on/off each outlet. Advanced network management features allow for remote access and integration with accessories including environmental monitoring and security access solutions.



### PDU Function

Metering Attributes	Voltage(V), Current(A), Apparent Power(kVA), Real Power(kW), Power Factor, Energy (kWh)
Metering Accuracy	± 1% to ISO/IEC 62052-21
Metering Locations	Input phase and circuit breaker level measurements
Remote Outlet Switching	Yes

### Electrical Input

Input Plug Type	Dual Rated IEC60309 530/532P6 (IP44)
Acceptable input voltage	380 – 415 VAC, 3-phase
Input current (phase)	32/30 A (24 A derated)
Input frequency	50/60 Hz
Max Input power	22.1 /17.3kVA

### Electrical Output

Output voltage	220 - 240 VAC
Maximum output current (phase)	32/30 A (24 A derated)
Overload protection (internal)	(6) 1-pole, 20 A, 5 kAIC, "temp stable, hy-mag type"
Outlet configuration	24 (C13/C15), 24 (4-in-1 Combo)

### Physical

Chassis Dimensions (L x W x D)	1780.0 × 56.0 × 75.0 mm (70.08 × 2.20 × 2.95 in)
Depth at circuit breaker	75 mm (2.95 in)
Input cord length	1.8m (5.91')

### Environmental

Operating Temperature	-5 to 60°C (23 to 140°F)
Storage Temperature	-20 to 60°C (-4 to 140°F)
Humidity (operating/storage)	5-90% RH / 5-95% RH; non-condensing
Max operating elevation, above MSL	3,000 m (9,840 ft)

### Compliance

Safety & Environmental	IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.
------------------------	--


## Advanced Network Management Module – RackPower PDU

### Network Connectivity

Network Connectivity	Dual ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address
Ethernet Cascading	Up to 64 units share a single “daisy-chain” Ethernet connection/IP address
DC Power Sharing	Each PDU can provide DC power sufficient to power network management electronics
Dual Ethernet Support	Dual Ethernet ports for redundant network communications
Dual Network Access	Dual network connectivity allows redundancy and/or multiple stakeholder connectivity
Remote Connectivity	HTTP(s), iP4V and iPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S),
WebUI Interface	Data efficient REACT framework with native mobile device support

### Management Module Attributes

Microprocessor/Memory	Cortex A-5
Field Replacement	Hot swap replaceable module; fast plug-and-play connectivity
Module Orientation	Tool-less removal and 180° install capable for top or bottom power cord orientation
User Display	Dual Displays: large high visibility LED display for key metering information and alarms. Low-power graphical oLED with user controls for local information.
Display Language	English, Spanish, German, French, Italian, Korean, Japanese, Chinese (simplified)
Lighted Color Code	User programmable color border allows power source identification by PDU
Sensor & Supports	Supports up to 8 digital sensors for environmental sensors and/or electronic locks



# Model: RP2850


32/30 A (24 A derated), 380 – 415 VAC, 3-phase Wye



## Overcurrent Protection

### Circuit Breaker Configuration

Circuit Breaker Type	(6) 1-pole, 20 A, 5 kAIC, "temp stable, hy-mag type"
Circuit Interrupt Rating	5 kAIC
Circuit Breaker Trip Curve	Sensata Trip Curve 62/Carling Trip Curve 24
Inrush Pulse Tolerance	10 times rated current (approx.)
Dielectric Strength	3,750 VAC, 60Hz, 60 seconds between all electrically isolated terminals
Vibration	Shall not trip when vibrated to MIL-STD-202, Method 204, Condition A, 100% load
Temperature Rating	-40 to 85°C (-40 to 185°F) Ambient
Handle Off Guard	Yes, protects against accidental user actuation to OFF position



### Environmental Sensors and Security Access Control

EA9102	Single Temperature Probe
EA9103	Temperature and Humidity Combo Sensor
EA9105	3x Temperature and Humidity Combo Sensor
EA9106	Sensor Input Hub (3 sensors input to PDU)
EA9109	Magnetic Door Switch (open/close)
EA9110	Dry Contact Cable (for third party sensors)
EA9111	Spot Fluid Leak Sensor
EA9112	Rope Fluid Leak Sensor
EA9116	Smoke Alarm Sensor
EA9500	Security Access eHandle supports physical key entry + Electronics access + RFID card reader + Keypad
EA9502	Security Access eHandle supports physical key entry + Electronics access + RFID card reader
EN9550	eHandle Sensor, Temperature and Door Contact Combo Sensor
EN9551	eHandle Sensor, 3x Temperature and Door Contact Combo Sensor

### Warranty and Terms

**Warranty :** nVent warranties RackPower brand equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser. For full warranty details, please visit <https://enlogic.com/warranty>.

**Disclaimer:** Copyright© 2023, nVent Electric plc and/or its affiliates. All rights reserved. This document is provided for information purposes only and current at the time of publishing; the contents hereof are subject to change without notice. This document is not warranted to be error-free, nor subject to any other warranties or conditions, whether expressed orally or implied in law, including implied warranties and

conditions of merchantability or fitness for a particular purpose. We specifically disclaim any liability with respect to this document, and no contractual obligations are formed either directly or indirectly by this document. This document may not be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, without our prior written permission.

#### North America

##### All locations

Tel +1.800.525.4682

#### Europe

##### Germany

Tel +49.7082.794.0

##### France

Tel +33.388.90.64.90

##### Sweden, Norway,

##### Finland

Tel +46.8.683.61.00

##### UK, Ireland

Tel +44.144.2218.768

##### Poland

Tel +48.22.209.98.35

##### Italy

Tel +39.02.932.714.1

#### Asia Pacific

##### VR China

Tel +86.21.2412.6943

##### Singapore

Tel +65.6768.5800

##### Japan

Tel +81.45.476.0271

#### Middle East & India

##### United Arab Emirates

Tel +971.4.823.8666

##### India

Tel +91.80.6715.8900

##### Turkey

Tel +90.541.3680941



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**