

nVent SCHROFF Rail Wallmount Enclosure



CONNECT AND PROTECT

Railway ready EN50125-3 certified pole-mount stainless steel enclosure for integrated wayside radio, fiber splice, access point and power distribution applications



PRODUCT SPECIFICATION/TECHNICAL DATA

Material:	AISI 304L stainless steel (316L optional)
Finish:	RAL 7035 powder painting UV resistant.
Body:	Folded and seam welded 1.5 mm/16 gauge thick stainless steel structure, pre-equipped with M8 blind rivet nuts for wall and pole mounting.
Door:	Corner formed in one piece, 2 mm/14 gauge stainless steel door with 180° left/right opening with door stopper.
Roof:	Rain & Sun hood to protect against adverse weather conditions
Lock:	Swing handle with anti-vibration mechanism equipped with DIN profile half cylinder Ronis 2131A lock and Espagnolette two points locking (3 points also available on request).
Cable access:	Gland plate on the bottom. Cut-outs can be requested based on project specific requirements.
Protection:	Up to NEMA Type 12; NEMA Type 13; NEMA Type 4X; IP66; IK10
Internal accessories:	Standard: Document Pocket A4 Optional: 19" uprights on the front, Mounting plate in the rear
External accessories:	Optional: Lifting eyes, wall/pole mount kits
Additional information:	For outdoor environments, the use of a pressure compensation breather is advised. Also in environments known for quick temperature changes, condensation should be taken into consideration.

Standard BOM:	<ul style="list-style-type: none"> 1 SWR body – 1.5 mm stainless steel 1 SWR door – 2 mm stainless steel 2 Stainless steel 180° Hinges 1 Swing handle with Espagnolette two points locking 1 DIN profile half cylinder Ronis 2131A lock 1 Door Switch 1 Door Stopper/Gas Spring 1 Earthing cable M8 x M8, length 300 mm 1 Rain & Sun Roof 1 Gland plate with pressure compensation breather and grounding stud M6 1 Document pocket A4/legal
----------------------	---

Optional equipment:	<ul style="list-style-type: none"> 19" brackets for 600 W cabinets Mounting panel on the rear LED Lamps Wall-mount/Pole-mount Kits Lifting Eyes Pre-wired Power Distribution Kits (PDU)
----------------------------	---

COMPREHENSIVE SET OF STANDARD PREDEFINED CONFIGURATIONS

Dimension (H x W x D)	SKUs
600 x 400 x 210	SRW0604021
600 x 600 x 210	SRW0606021
600 x 600 x 300	SRW0606030
800 x 600 x 210	SRW0806021
800 x 600 x 300	SRW0806030

Broad range of standard cabinet dimensions added with elaborate integration capability, allow easy and fast project specific designs and reduced delivery times.



North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 info@nVent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.603
 info@nVent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 info@nVent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 info@nVent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER